

K6S Vacuum chamber machine

Technical data sheet

Functional perfection

Cost-effective, easy to operate, space-saving and designed overall for hygiene. This mobile free-standing model has been operating reliably for years and packs the most diverse products in bags. Whether you're a butcher or an industrially equipped fruit or vegetable processor – you can be sure that all products are securely packed. The K6S processes the desired production volume with high reliability – even in harsh production environments.



Facts

| | |
|--|---|
| Usable chamber size | 920 x 480 x 214 mm* |
| External dimensions without panel | 1189 x 969 x 1084 mm* |
| Welding strip lengths | 920 mm / 480 mm |
| Weight with pump | 496 kg |
| Machine cycle | up to 3 cycles/min |
| Electrical connection | 400 V / 3 / 50 Hz / 9 kW** |
| Compressed air | |
| Operating pressure | 6 bar |
| Compressed air consumption | 4 NL/cycle |
| Hose connection | ID 9 mm |
| Vacuum pump | 205 m ³ /h |
| Welding and detachable technology | rom above counter strip below |
| Pre-ventilation (soft ventilation) | standard |
| Evaporation point sensor (H ₂ O sensor) | standard |
| MAP (inert gas option) | optional |
| Filler plates | standard |
| Automatic lid | standard |
| Types of evacuation | up to evaporation up to setpoint in steps up to setpoint timed (emergency operation) |
| Trolley | yes |
| Bag residue extraction | no |

* Width x depth x height
** Voltage variants on request
Subject to technical changes



Usable product area



K6S Vacuum chamber machine:



Hygienic design
Easy operation
Service-friendly

Wireless, click-in welding strips
are built into the lid

Raised suction socket in the chamber lid

Separately controllable
welding and detachable
seam

Evaporation point recognition,
staged vacuuming, intermediate
ventilation, pre-ventilation:
Energy cost savings and maximum
product quality

Multilingual user interface

Password protection for
stored recipes (programs)


Automatic cycle start
on closing the lid

Trolley



Options & accessories

1. VC999 chamber machines are also available with modified atmosphere packaging
2. Insert for the packaging of liquids
3. Pump mounted externally to reduce noise, odour and heat
4. Extension to manual shrink line
5. Filling shovels



Packaging material | The right bag for the customer's every need

